


Oven-Controlled Crystal Oscillator YOV2525DP OCXO

Applications

- base station
- Medical equipment

Features

- Small size, high cost-performance, localized production
- Aging $\leq 0.2\text{ppb/day}$
- Temperature stability $\leq \pm 0.2\text{ppb}$ (-40°C to 85°C)



Specifications (规格参数)

Item		Technical Specifications
Performance Specifications 性能指标	Frequency 频率	5~100MHz
	Supply Voltage 工作电压	3.3V, 5V, 12V
	Output waveform 波形	Sine Wave/HCMOS
	Frequency Tolerance vs.Operating Temperature Range 温度稳定度	≤±0.2 ppb (best achievable) @-40~+85℃
	Warm up current 启动功耗	<4W
	Steady Consumption 稳定功耗	<2W
	Warm up time 启动时间	<5min
	Voltage Control Characteristics 电压控制特性	Linearity <5%
		Positive
Phase Noise相噪 (@10M)	10Hz	-120dBc/Hz Min.
	100Hz	-140dBc/Hz Min.
	1kHz	-155dBc/Hz Min.
	10kHz	-160dBc/Hz Min.
	100kHz	-160dBc/Hz Min.
	1MHz	-160dBc/Hz Min.
Environmental Conditions 工作环境	Operating Temperature Range 工作温度	-40℃~85℃
	Storage Temperature Range 储存温度	-55℃~105℃
Vibration 振动	Test conditions: Amplitude: 0.75mm (5~26HZ); Acceleration: 10g; 10Hz~500Hz; 30min a cycle, 2 hours in each direction (3 directions, X, Y and Z), IEC68-2-06 Test Fc.	
Shock 冲击	50g; 11ms; Half-sine wave (3 directions, X, Y, and Z), IEC68-2-27TestEa/Severity 50A	
Size 尺寸	25.4*25.4*12.7mm	

Note: The specifications are for reference only. Please contact customer service for detailed specifications.